

### drum-tec pro 3 Triggersettings (for maximum articulation)

| V71          | Type   | Sensitivity | Threshold | Curve  | Scan Time | Retrig Canc. | Mask Time | Rim Gain | Head/Rim Adj. | Head POS | Rim POS | X-Stick Adj. |
|--------------|--------|-------------|-----------|--------|-----------|--------------|-----------|----------|---------------|----------|---------|--------------|
| pro3 Kick    | KD-140 | 4           | 10        | EXP2   | 2,8       | 10           | 10        | -        | -             | -        | -       | -            |
| pro3 Snare   | PD-128 | 6,5         | 2         | LINEAR | 2,2       | 4            | 9         | 1        | 15            | on       | on      | 110          |
| pro3 Tom 8"  | PD-10X | 5           | 2         | EXP1   | 2,8       | 4            | 9         | 1,1      | 20            | off      | on      | -            |
| pro3 Tom 10" | PD-10X | 6           | 2         | EXP1   | 2,8       | 4            | 9         | 1,5      | 20            | off      | on      | -            |
| pro3 Tom 12" | PD-12X | 5           | 2         | EXP1   | 3,2       | 4            | 9         | 1,2      | 12            | off      | on      | -            |
| pro3 FT      | PD-12X | 5           | 2         | EXP1   | 3,2       | 4            | 9         | 1,2      | 12            | off      | on      | -            |

### drum-tec pro 3 Triggersettings (for non hotspot and tuning ability)

| V71          | Type     | Sensitivity | Threshold | Curve  | Scan Time | Retrig Canc. | Mask Time | Rim Gain | Head/Rim Adj. | Head POS | Rim POS | X-Stick Adj. |
|--------------|----------|-------------|-----------|--------|-----------|--------------|-----------|----------|---------------|----------|---------|--------------|
| pro3 Kick    | KD-140   | 4           | 10        | EXP2   | 2,8       | 10           | 10        | -        | -             | -        | -       | -            |
| pro3 Snare   | PD-128   | 6,5         | 2         | LINEAR | 2,2       | 4            | 9         | 1        | 15            | on       | on      | 110          |
| pro3 Tom 8"  | PDA-100  | 6           | 2         | LINEAR | 2         | 3            | 11        | 1        | 18            | -        | on      | -            |
| pro3 Tom 10" | PDA-100  | 6           | 2         | LINEAR | 2         | 3            | 11        | 1        | 18            | -        | on      | -            |
| pro3 Tom 12" | PDA-120  | 5           | 2         | LINEAR | 2,8       | 5            | 9         | 0,9      | 16            | -        | on      | -            |
| pro3 FT      | PDA-140F | 5           | 2         | LINEAR | 2,8       | 9            | 4         | 1,1      | 14            | -        | on      | -            |